

Project Name

Location

Prepared By



## NUVO 65-682

40W LED AREA LIGHT W/PHOTOCELL

Notes

[www] 11-12-2020 00:15:03

### General

Status	Active
Finish	Gray
Wattage	40
Lumen Output	5600L - 6400L
CCT (Kelvin)	3000K/4000K/5000K
IP Rating	IP65
Indoor or Outdoor Fixture	Outdoor

### Specifications

Technology	LED
CRI	70
Voltage	120V-277V
Beam Angle	150x150
Rated Hours	50000
Operating Temperature	-40C (-40F) to a maximum of +50C (+122F)
Dimmable	1-10V Dimmable
Photocell	Yes
Surge Protection	Built-in surge protection - 2KV
Weight (lb.)	4.85
Material	Aluminum

### Dimensions

Height (in.)	7.36
Width (in.)	9.13
Extension (in.)	13.62

### Compliance

Safety Listing	cULus
Location Rating	Wet
CEC Status	Lawful for sale in California
RoHS Compliant	Yes

### Additional Information

Additional Information	Type V Lighting Distribution; Dusk to Dawn Lamp
Installation Notes	Suitable for 42-60mm pipe installation
Warranty	5 Year Limited - Fixtures