## SATCO NUVO

Project Name

Location

Prepared By



## **SATCO S29446**

15PAR38/LED/40/930/120V

Notes

www.i 08-31-2020 01-09-32

General	
Status	Active
Watts	15
Incandescent Equivalent	90
Fluorescent Equivalent	90
Volts	120V
Shape	PAR38
Base	Medium
ANSI Base	E26
Finish	Silver
CCT (Kelvin)	3000
Temperature	Warm White
CRI	90
Lumens	1200
Beam Spread	40
Dimmable	Yes - Dimmable
Hours Rated	25000
Lamp Type	PAR
Technology	LED

Electrical	
Operating Frequency	60 Hz
CBCP	1533
Dimming Type	Thyristor
Power Factor	0.9
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

Physical	
MOL	5.00
MOD	4.72
Lensed	Lensed Lamp
Lens Finish	Clear
Lens Material	Thermo Plastic
Housing Color	Silver

Additional Information	
Enclosure Rating	Enclosed Rated Lamp
Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited - 12 hr per day

Compliance	
Safety Listing	cULus
Location Rating	Wet
Energy Star	Pending
CEC Status	California T24 Compliant
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED Lamp

















