



SIGN UP / LOG IN



View More +

NEW 

# M18 FUEL™ 2-Tool Combo Kit

Our M18 FUEL™ two-tool combo kit delivers the most advanced 18-Volt cordless cutting, drilling and fastening power tool technology in the industry. This kit features two M18 FUEL™ 18-Volt lithium-ion brushless cordless tools including our ½ in. Hammer Drill/Driver (2804-20) and our SURGE™ 1/4" Hex Hydraulic Driver. Our M18 FUEL™ tool system is fully compatible with the MILWAUKEE® M18™ 18-volt cordless system. These power tools feature the most advanced cordless technology in the industry; a POWERSTATE™ Brushless Motor, REDLINK PLUS™ Intelligence tool technology, and REDLITHIUM™ Battery Technology, resulting in longer motor life, longer run time and more power. Our two-tool kit also includes two M18™ REDLITHIUM™ XC5.0 batteries, one M18™ and M12™ multi-voltage charger, a side handle, three belt clips, two bit holders, and one heavy-duty contractor bag.

Close

## INCLUDES:

- (1) M18 FUEL™ SURGE™ 1/4" Hex Hydraulic Driver (2760-20) (/Products/Power-Tools/Fastening/Impact-Drivers/2760-20)
- (1) M18 FUEL™ ½" Hammer Drill/Driver (Tool Only) (2804-20) (/Products/Power-Tools/Drilling/Hammer-Drills/2804-20)
- (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Pack (48-11-1850) (/Products/Batteries-and-Chargers/M18-Batteries-and-Chargers/48-11-1850)
- (1) M18™ & M12™ Multi-Voltage Charger (48-59-1812) (/Products/Batteries-and-Chargers/M12-Batteries-and-Chargers/48-59-1812)
- (1) Carrying Case
- (1) Side Handle
- (2) Belt Clip
- (2) Bit Holder
- Close

[Where To Buy](#)

## WHAT'S INCLUDED

## REVIEWS



**M18 FUEL™ 1/2" Hammer Drill/Driver (Tool Only)**  
**Cat. # 2804-20**



## M18 FUEL™ 1/2" Hammer Drill/Driver (Tool Only)

The M18 FUEL™ 1/2" Hammer Drill is the Industry's Most Powerful Drill by delivering Up to 60% More Power, Up To 1.5" Shorter length and Up To 2X Faster Speed Under Heavy Load. The POWERSTATE™ Brushless motor delivers 1,200 in-lbs of torque and 2,000 RPMs, providing fast drilling through demanding applications. At 6.9" in length, this is the most compact drill in its class, giving better access in tight spaces and reducing fatigue. The REDLINK PLUS™ intelligence ensures maximum performance and protects from overloads, heating and over-discharge. The REDLITHIUM XC5.0™ Battery Pack delivers more work per charge and more work over the life of the pack when compared to competitors. The all metal ratcheting chuck is the best in class by providing increased bit grip strength and corrosion resistance.

### Features

**POWERSTATE™ Brushless Motor:** Purposely built for the M18 FUEL™ 1/2" Hammer Drill to provide Up To 60% More Power than the competitive set

**REDLINK PLUS™ Intelligence:** Ensures optimal performance and provides overload protection to prevent damage to the tool and battery during heavy applications while still maintaining compatibility across the entire M18™ System.

**REDLITHIUM™ XC5.0 Battery Pack:** Delivers more work per charge and more work over the life of the pack than competitors

Up To 60% More Power: 1,200 in-lbs of torque

Only 6.9" in length for access into tight spaces and reduced fatigue

LED on foot of tool for better lighting in dark spaces



Compatible with all M18™ batteries

 [Download Owner's Manual \(https://documents.milwaukeetool.com/58-14-0478d1.pdf\)](https://documents.milwaukeetool.com/58-14-0478d1.pdf)

|  [Download Service Parts List \(https://documents.milwaukeetool.com/54-24-5010.pdf\)](https://documents.milwaukeetool.com/54-24-5010.pdf)

PRODUCT SPECIFICATIONS

Battery System	M18
Voltage	18V
Length	6.9"
RPM	0-550/ 0-2,000
Peak Torque	1200 in-lbs
BPM	32,000
Number of Clutch Settings	14
Chuck Type	1/2" All Metal Ratcheting
Tool Warranty	5 Years
Weight	3.2 lbs (Tool Only)
Power Source	Cordless



**M18 FUEL™ 1/4" Hex Impact Driver (Tool Only)**  
**Cat. # 2853-20**

You Might Also Like



SHOCKWAVE™ Impact  
Duty Drill & Drive Set -  
40PC



M18™ Six Pack Sequential  
Charger

(/Products/Accessories/Driving-and-Chargers/M18-and-  
(/Products/Batteries-