

Project Name

Location

Prepared By



Notes

[www] 11-02-2020 01:57:04

General

Status	Active
Finish	White
Wattage	16.5
CCT (Kelvin)	3000K/4000K/5000K
Width (in.)	11.54
Height (in.)	3.04
Indoor or Outdoor Fixture	Indoor

Specifications

Technology	LED
CRI	90
Lumen Output	990L - 1100L
Rated Hours	50000
Voltage	120V
Weight (lb.)	1.21
Fixture Material	Acrylic
Fixture Type	Flush Mount
Operating Temperature	-20C (-4F) to a maximum of +40C (+104F)

Compliance

Safety Listing	cETLus
Location Rating	Damp
Energy Star	Pending
CEC Status	Lawful for sale in California
RoHS Compliant	Yes
FCC Compliant	Yes

Additional Information

Warranty	5 Year Limited - Fixtures
----------	---------------------------