

Project Name

Location

Prepared By



## SATCO S38939

60W/LED/HID/TEMP/5K/120V

### Notes

[www] 11-09-2020 01:10:24

### General

Status	Active
Watts	60
Incandescent Equivalent	300
HID Equivalent	200
Volts	120V
Shape	Comcob
Base	Plug 3-Prong
ANSI Base	Plug
Finish	Orange
CCT (Kelvin)	5000
Temperature	Natural Light
CRI	80
Lumens	6000
Beam Spread	300
Dimmable	Non-Dimmable
Hours Rated	50000
Lamp Type	Work Light
Technology	LED

### Electrical

Operating Frequency	50-60 Hz
Power Factor	0.9
Operating Temperature	-30C (-22F) to a maximum of +60C (+140F)

### Physical

MOL	9.2
MOD	5.12
Lens Finish	Frosted
Lens Material	Plastic
Weight (lb.)	2.77

### Additional Information

Additional Info	Linkable up to 10 sets
Rated For Enclosed Fixture	No
IP Rating	IP64
Specification Note	6 ft. wire between units
Warranty	5 Year Limited - Hi-Pro

### Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	No
CEC Status	Lawful for sale in California
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp

