



Representative Image

## Alternate Catalog No. PSR6-600-70 Catalog No. 1SFA896104R7000

Description: "PSR SOFTSTARTER 6,1A CTRL 110-240V"

UPC No 7320500338209

Home > Drives and Soft Starters > Softstarter - Open (PSR)

**PSR softstarter - The compact range** The PSR softstarter range is a simple yet reliable starting solution that utilizes only the most basic of soft starting features: soft start and stop. It performs well in applications requiring many starts per hour and is perfect for installations where you need to save space. **Main benefits\*** Small and compact starting solution\* Can perform many starts per hour\* Reduce energy loss at full speed with built-in bypass. **Main features\*** Rated operational current: 3 to 105 A\* Operational voltage: 208-600 V AC\* Control supply voltage: 24 V AC/DC or 100-240 V AC.

### Descriptors

Category	Softstarter - Open (PSR)
----------	--------------------------

### Specifications

Product Type	Soft Starters
Input Voltage	208-600 V
Control Voltage	100-240 V
Normal Duty: Output Current (A)	6.1
Normal Duty: Motor Power (HP) at 460V	3
Power Dissipation In Watts	2.9

### Classifications

RoHS Indicator	Yes
UL/CUL Listing	Yes

### Dimensions

Height (in)	5.5
Width (in)	1.8
Depth (in)	4.5
Weight (lb)	0.99
Height (mm)	140
Width (mm)	45
Depth (mm)	113.5
Weight (kg)	0.45