

# Internal Product Specification Sheet

## Velcro® Brand Hook Fastener

### Material Description

Name: Hook 088-0199  
Material: Nylon with an acrylic base binder adhesive

### Dimensional Specifications

Thickness: 0.068 inches (minimum)  
Roll Length: <100 yards (-0, +12 inches)  
= / >100 yards (-0, + 1% of target value)

Contact your Customer Relations Specialist for available colors and widths

### Performance Specifications

Testing	Minimum	Test Method
Closure Peel Strength	1.0 PIW	40011
Closure Shear Strength	8.0 PSI	40012

Tested with: Loop 1000

**The preparation, testing and conditioning follow the Velcro USA Inc. Quality Control Laboratory Standard Procedures.**

**Note: The following information should be considered representative and is intended to be used as a reference only. This information should not be used for specification purposes.**

Rev. Date: 11.14.16