

Lighting

PHILIPS

AmbiStar

AMBISTAR ELE BALLAST (2) F40T12 120V

Ambistar electronic ballasts are an easy-to-install, energy-efficient replacement solution for optimizing residential and hospitality lighting.

Product data

General Information				
Lamp Type	F40T12			
Number of Lamps	1/2 piece/unit			
Ballast Type	Electronic Fluorescent			
Base Model	RELB2S40N			
Suitable For Outdoor Use	Yes			
Automatic Restart	Yes			
Operating and Electrical				
Input Voltage	120 V			
Input Frequency	60 Hz			
Max THD	20 %			
Starting Method	Rapid Start			
Lamp Current Crest Factor (Nom)	1.7			
Ignition Time (Nom)	1s			
Ballast Factor (Nom)	0.85			
Power Factor (Nom)	0.98			
Input Current (Operating) (Nom)	0.62 A			
Input Power (Nom)	72 W			
Rated Lamp Watts	40 W			
Wiring				
Color Input Terminals	No terminals			
Color Output Terminals	No terminals			
Wire Striplength	0.50/0.375 mm			


Lamp Connection	Series			
Wire Length by Color	See data sheet			
Wire Gauge (Nom)	18AWG mm			
Wire Type	Solid			
Remote Wiring Configuration Allowed	Yes			
Tandem Wiring Configuration Allowed	Yes			
Through Wiring Configuration Allowed	Yes			
Max Ballast-Lamp Distance Remote Wiring	20'			
Max Ballast-Lamp Distance Tandem Wiring	Red = 10'			
Max Ballast-Lamp Distance Through Wiring	Red = 10'			
Connector Type	No connector			
Temperature				
T-Case Maximum (Nom)	70 °C			
Mechanical and Housing				
Housing Material	Metal			
Housing	N			
Housing Dimensions	9.5" x 1.3" x 1.0"			
Approval and Application				
EMC Immunity Standard	FCC Consumer			
Approbation Marks	CSA certificate UL certificate CEC Listing			
	Circle E logo CSA E DOE Energy Star RoHS			
	Compliant			

AmbiStar

Sound Rating	А
UL Recognized	No
Product Data	
Order product name	AMBISTAR ELE BALLAST (2) F40T12 120V
EAN/UPC - Product	781087090428
Order code	RELB2S40N35M

Numerator - Quantity Per Pack	1		
Numerator - Packs per outer box	30		
Material Nr. (12NC)	913701218102		
Net Weight (Piece)	359.000 g		

Dimensional drawing



Product	A1	A2	B1	C1
AMBISTAR ELE BALLAST (2) F40T12 120V	9.50 in	8.90 in	1.30 in	1.00 in



© 2019 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

www.lighting.philips.com 2019, March 22 - data subject to change