



SignPRO

SIGNPRO MAG ELE SIGN BAL (1-4)T12HO 10-40FT 120-277V

Philips Advance signPRO line...a brand synonymous with full-line, high-quality sign ballasts offered exclusively to the sign industry to support the market's broad range of sign applications, now adds: ...four new energy-efficient signPRO Electronic Fluorescent Sign Ballasts for T8/HO and T12/HO High Output (800mA) Lamps. Philips Advance signPRO line...a brand synonymous with full-line, high-quality sign ballasts offered exclusively to the sign industry to support the market's broad range of sign applications, now adds: ...four new energy-efficient signPRO Electronic Fluorescent Sign Ballasts for T8/HO and T12/HO High Output (800mA) Lamps.

Product data

General Information			
Lamp Type	T12/HO		
Number of Lamps	1-4 piece/unit		
Lamp Footage	10 - 40 FT		
Ballast Type	Electronic Fluorescent		
Base Model	ISB104014EI		
Suitable For Outdoor Use	Yes		
Automatic Restart	Yes		
Operating and Electrical			
Input Voltage	120 to 277 V		
Input Frequency	50 to 60 Hz		
Max THD	10 %		
Starting Method	Instant Start		
Lamp Current Crest Factor (Nom)	1.7		
Ignition Time (Nom)	0.1 s		
Ballast Factor (Nom)	0.61		
Power Factor (Nom)	0.98		

Input Current (Operating) (Nom)	2.88 A
Input Power (Nom)	337 W
Rated Lamp Watts	110 W
Wiring	
Wire Striplength	0.50/0.375 mm
Lamp Connection	Parallel
Wire Length by Color	See data sheet
Wire Gauge (Nom)	18AWG mm
Wire Type	Solid
Remote Wiring Configuration Allowed	No
Tandem Wiring Configuration Allowed	No
Through Wiring Configuration Allowed	Yes
Max Ballast-Lamp Distance Remote Wiring	No Remote
Max Ballast-Lamp Distance Tandem Wiring	No Tandem
Max Ballast-Lamp Distance Through Wiring	Any = 20'


Datasheet, 2019, March 22 data subject to change

SignPRO

Mechanical and Housing	
Housing Material	Metal
Housing	BL2
Housing Dimensions	14.31" x 3.19" x 2.63"
Approval and Application	
EMC Immunity Standard	FCC Non-Consumer
Approbation Marks	CSA certificate UL certificate RoHS
	Compliant
Sound Rating	А
UL Recognized	No

Product Data	
Order product name	SIGNPRO MAG ELE SIGN BAL (1-4)T12HO
	10-40FT 120-277V
EAN/UPC - Product	781087135808
Order code	ISB104014EI
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	913701262501
Net Weight (Piece)	4.523 kg

Dimensional drawing



Product	A1	A2	B1	C1
SIGNPRO MAG ELE SIGN BAL (1-4)T12HO	14.31 in	13.75 in	3.19 in	2.63 in
10-40FT 120-277V				



© 2019 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.