

Alternate Catalog No. PSE45-600-70
Catalog No. 1SFA897105R7000

Description: "PSE45, 600V, 100-250VAC"

UPC No 7320500400630

Home > Drives and Soft Starters > Softstarter - Open (PSE)

PSR softstarter - The compact rangeThe PSR softstarter range is a simple yet reliable starting solution that utilizes only the most basic of soft starting features: soft start and stop. It performs well in applications requiring many starts per hour and is perfect for installations where you need to save space.**Main benefits*** Small and compact starting solution* Can perform many starts per hour* Reduce energy loss at full speed with built-in bypass.**Main features*** Rated operational current: 3 to 105 A* Operational voltage: 208-600 V AC* Control supply voltage: 24 V AC/DC or 100-240 V AC.



Descriptors

Category	Softstarter - Open (PSE)
----------	--------------------------

Specifications

Product Type	Soft Starters
Input Voltage	208-600 V
Control Voltage	100-240 V
Normal Duty: Output Current (A)	42
Normal Duty: Motor Power (HP) at 208V	10
Normal Duty: Motor Power (HP) at 230V	15
Normal Duty: Motor Power (HP) at 460V	30
Normal Duty: Motor Power (HP) at 575V	40
Heavy Duty: Output Current (A)	34
Heavy Duty: Motor Power (HP) at 208V	10
Heavy Duty: Motor Power (HP) at 230V	10
Heavy Duty: Motor Power (HP) at 460V	25
Heavy Duty: Motor Power (HP) at 575V	30
Power Dissipation In Watts	1.2

Classifications

RoHS Indicator	Yes
UL/CUL Listing	Yes

Dimensions

Height (in)	9.6
Width (in)	3.5
Depth (in)	7.2
Weight (lb)	5.3
Height (mm)	245
Width (mm)	90
Depth (mm)	183.5

Dimensions

Weight (kg)

2.4