

Project Name

Location

Prepared By



# SATCO S11255

9.5BR30/LED/RGB/TW/SF

## Notes

[www] 01-19-2021 00:51:03

### General

Status	Active
Watts	9.5
Incandescent Equivalent	65
Volts	120V
Shape	BR30
Base	Medium
ANSI Base	E26
Finish	White
CCT (Kelvin)	2700K-5000K
Temperature	Warm to Cool White/Color Changeable
CRI	80
Lumens	800
Beam Spread	100
Dimmable	Dimmable Only with Starfish App
Hours Rated	25000
Lamp Type	Reflector
Technology	LED

### Smart Product Info

IOT Enabled	Yes
Voice Assistants Supported	Siri; Alexa; Hey Google; SmartThings

### Electrical

Operating Frequency	60 Hz
---------------------	-------

### Specifications

Dimming Type	Smart
Power Factor	0.6
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

### Physical

MOL	5.12
MOD	3.70
Weight (lb.)	0.21

### Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited - 3 hr per day

### Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	Yes
ES Unique ID	ESID-2368817
California Status	Non-Compliant
Nevada Status	Lawful for sale in Nevada
RoHS Compliant	Yes

FCC Compliant

Yes

SDS Sheet

LED\_Lamp

