

## Eaton, 22.5 mm RMQ-Titan Pushbutton

M22-D-Y

UPC:786685275963

### Dimensions:

- **Height:** .39 IN
- **Length:** 1.17 IN
- **Width:** 1.17 IN

**Weight:**.995 LB

**Notes:**Includes contact block mounting adapter.

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** Pushbutton
- **Action:** Momentary
- **Actuator:** Flush, Button
- **Actuator Color:** Yellow
- **Bezel:** Silver
- **Enclosure:** IP67, IP69K
- **Environmental Rating:** IP67, IP69K, NEMA 4x, 13
- **Illumination:** Non-illuminated
- **Mounting:** Flush
- **Nema Rating:** NEMA 4X, 13
- **Operating Cycles:** 5,000,000 operations
- **Size:** 22.5 mm
- **Product Category:** Flush pushbutton
- **Series:** M22

### Supporting documents:

- [Eaton's Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)



- [M22 Operators and Accessories](#)
- [M22 Pilot Devices](#)
- [Eaton Specification Sheet - M22-D-Y](#)
- [Global Data Sheet - M22-D-Y](#)

**Certifications:**

- CSA Certified
- CCC Marked
- Lloyd's Register Certified

**Product compliance:**

- Bureau Veritas
- CE Marked
- GoST-R