

Project Name

Location

Prepared By



**Notes**

[www] 01-25-2021 01:02:00

**General**

Status	Active
Finish	White
Wattage	10
CCT (Kelvin)	2700K-5000K
Color Temperature	Warm to Cool White
Width (in.)	7.36
Height (in.)	2.89
Indoor or Outdoor Fixture	Indoor

**Smart Product Info**

IOT Enabled	Yes
Voice Assistants Supported	Siri Shortcuts; Alexa; Hey Google; SmartThings

**Specifications**

Technology	LED
CRI	90
Lumen Output	800
Rated Hours	25000
Voltage	120V
Dimmable	Dimmable Only with Starfish App
Recommended Dimmer	Smart
Beam Angle	95
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)
IC Rated	Yes
Weight (lb.)	0.71
Fixture Shape	Round
Fixture Material	Metal
Fixture Type	Downlight Retrofit

**Compliance**

Safety Listing	cULus Classified; cULus Listed
Location Rating	Wet
Energy Star	Yes
ES Unique ID	ESID-2371662
California Status	California T24 Compliant
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

**Additional Information**

Includes	E26 Adapter
Warranty	5 Year Limited - 3 hr per day