

Project Name

Location

Prepared By



Notes

[www] 01-25-2021 01:02:05

General

Status	Active
Finish	White
Wattage	10
CCT (Kelvin)	2700K-5000K
Color Temperature	Warm to Cool White
Width (in.)	5.31
Height (in.)	1.50
Indoor or Outdoor Fixture	Indoor

Smart Product Info

IOT Enabled	Yes
Voice Assistants Supported	Siri Shortcuts; Alexa; Hey Google; SmartThings

Specifications

Technology	LED
CRI	80
Lumen Output	650
Rated Hours	25000
Voltage	120V
Dimmable	Dimmable Only with Starfish App
Recommended Dimmer	Smart
Beam Angle	110
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)
IC Rated	Yes
Weight (lb.)	0.81
Fixture Shape	Round
Fixture Material	Steel
Fixture Type	Downlight Retrofit

Compliance

Safety Listing	cETLus
Location Rating	Wet
Energy Star	Yes
ES Unique ID	ESID-2371663
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

Additional Information

Warranty	5 Year Limited - 3 hr per day
----------	-------------------------------