

Project Name

Location

Prepared By



Notes

[www] 01-25-2021 01:02:00

General

Status	Active
Finish	White
Wattage	20
CCT (Kelvin)	3000K-6500K
Color Temperature	Warm to Cool White
Length (in.)	72.00
Width (in.)	0.47
Height (in.)	0.12
Indoor or Outdoor Fixture	Indoor

Smart Product Info

IOT Enabled	Yes
Voice Assistants Supported	Siri Shortcuts; Alexa; Hey Google; SmartThings

Specifications

Technology	LED
CRI	80
Lumen Output	1600
Rated Hours	25000
Voltage	120V
Dimmable	Dimmable Only with Starfish App
Recommended Dimmer	Smart
Beam Angle	120
Operating Temperature	-20C (-4F) to a maximum of +40C (+104F)
Weight (lb.)	0.46
Fixture Material	Plastic
Fixture Type	Tape Light

Compliance

Safety Listing	cETLus
Location Rating	Damp
Energy Star	No
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

Additional Information

Installation Notes	Includes power supply: input: AC100 240-Volt 0.6A 50-60 Hz, output: 12-Volt, 20-Watt
Warranty	1 Year Limited - Smart Products