

Project Name

Location

Prepared By



Notes

[www] 01-25-2021 01:02:00

**General**

Status	Active
Finish	White
Wattage	8
CCT (Kelvin)	3000K-6500K
Color Temperature	Warm to Cool White
Length (in.)	36.00
Width (in.)	0.47
Height (in.)	0.12
Indoor or Outdoor Fixture	Indoor

**Smart Product Info**

IOT Enabled	Yes
Voice Assistants Supported	Siri Shortcuts; Alexa; Hey Google; SmartThings

**Specifications**

Technology	LED
CRI	80
Lumen Output	800
Rated Hours	25000
Voltage	120V
Dimmable	Dimmable Only with Starfish App
Recommended Dimmer	Smart
Beam Angle	120
Operating Temperature	-20C (-4F) to a maximum of +40C (+104F)
Weight (lb.)	0.09
Fixture Material	Plastic
Fixture Type	Tape Light

**Compliance**

Safety Listing	cETLus
Location Rating	Damp
Energy Star	No
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

**Additional Information**

Warranty	1 Year Limited - Smart Products
----------	---------------------------------