

Alternate Catalog No. PSTX37-690-70
Catalog No. 1SFA898204R7000

Description: "PSTX37, 690V, 100-250VAC"

UPC No 7320500501429

Home > Drives and Soft Starters > Softstarter - Open (PSTX)



Representative Image

Descriptors

Category	Softstarter - Open (PSTX)
----------	---------------------------

Specifications

Product Type	Soft Starters
Input Voltage	208-690 V
Control Voltage	100-250 V
Normal Duty: Output Current (A)	34
Normal Duty: Motor Power (HP) at 208V	10
Normal Duty: Motor Power (HP) at 230V	10
Normal Duty: Motor Power (HP) at 460V	25
Normal Duty: Motor Power (HP) at 575V	30
Heavy Duty: Output Current (A)	28
Heavy Duty: Motor Power (HP) at 208V	7.5
Heavy Duty: Motor Power (HP) at 230V	10
Heavy Duty: Motor Power (HP) at 460V	20
Heavy Duty: Motor Power (HP) at 575V	25
Power Dissipation In Watts	1.2

Classifications

RoHS Indicator	Yes
UL/CUL Listing	Yes

Dimensions

Height (in)	12.4
Width (in)	5.9
Depth (in)	7.7
Weight (lb)	13.4
Height (mm)	314
Width (mm)	150
Depth (mm)	197.5

Dimensions

Weight (kg)

6.1