

**Alternate Catalog No. PSTX170-690-70**  
**Catalog No. 1SFA898211R7000**

**Description: "PSTX170, 690V, 100-250VAC"**

**UPC No 7320500501443**

**Home > Drives and Soft Starters > Softstarter - Open (PSTX)**



Representative Image

**Descriptors**

Category	Softstarter - Open (PSTX)
----------	---------------------------

**Specifications**

Product Type	Soft Starters
Input Voltage	208-690 V
Control Voltage	100-250 V
Normal Duty: Output Current (A)	169
Normal Duty: Motor Power (HP) at 208V	50
Normal Duty: Motor Power (HP) at 230V	60
Normal Duty: Motor Power (HP) at 460V	125
Normal Duty: Motor Power (HP) at 575V	150
Heavy Duty: Output Current (A)	130
Heavy Duty: Motor Power (HP) at 208V	40
Heavy Duty: Motor Power (HP) at 230V	50
Heavy Duty: Motor Power (HP) at 460V	100
Heavy Duty: Motor Power (HP) at 575V	125
Power Dissipation In Watts	26

**Classifications**

RoHS Indicator	Yes
UL/CUL Listing	Yes

**Dimensions**

Height (in)	14.8
Width (in)	7.8
Depth (in)	9.3
Weight (lb)	21.2
Height (mm)	377
Width (mm)	199
Depth (mm)	238.3

## Dimensions

Weight (kg)

9.6