

Alternate Catalog No. PSTX250-690-70
Catalog No. 1SFA898213R7000

Description: "PSTX250, 690V, 100-250VAC"

UPC No 7320500501511

Home > Drives and Soft Starters > Softstarter - Open (PSTX)



Representative Image

Descriptors

Category	Softstarter - Open (PSTX)
----------	---------------------------

Specifications

Product Type	Soft Starters
Input Voltage	208-690 V
Control Voltage	100-250 V
Normal Duty: Output Current (A)	248
Normal Duty: Motor Power (HP) at 208V	75
Normal Duty: Motor Power (HP) at 230V	100
Normal Duty: Motor Power (HP) at 460V	200
Normal Duty: Motor Power (HP) at 575V	250
Heavy Duty: Output Current (A)	192
Heavy Duty: Motor Power (HP) at 208V	60
Heavy Duty: Motor Power (HP) at 230V	75
Heavy Duty: Motor Power (HP) at 460V	150
Heavy Duty: Motor Power (HP) at 575V	200
Power Dissipation In Watts	68

Classifications

RoHS Indicator	Yes
UL/CUL Listing	Yes

Dimensions

Height (in)	18.5
Width (in)	10.2
Depth (in)	10.9
Weight (lb)	28.0
Height (mm)	470
Width (mm)	258
Depth (mm)	279.1

Dimensions

Weight (kg)

12.7