

Alternate Catalog No. PSTX300-690-70
Catalog No. 1SFA898214R7000

Description: "PSTX300, 690V, 100-250VAC"

UPC No 7320500501481

Home > Drives and Soft Starters > Softstarter - Open (PSTX)



Representative Image

Descriptors

Category	Softstarter - Open (PSTX)
----------	---------------------------

Specifications

Product Type	Soft Starters
Input Voltage	208-690 V
Control Voltage	100-250 V
Normal Duty: Output Current (A)	302
Normal Duty: Motor Power (HP) at 208V	100
Normal Duty: Motor Power (HP) at 230V	100
Normal Duty: Motor Power (HP) at 460V	250
Normal Duty: Motor Power (HP) at 575V	300
Heavy Duty: Output Current (A)	248
Heavy Duty: Motor Power (HP) at 208V	75
Heavy Duty: Motor Power (HP) at 230V	100
Heavy Duty: Motor Power (HP) at 460V	200
Heavy Duty: Motor Power (HP) at 575V	250
Power Dissipation In Watts	97

Classifications

RoHS Indicator	Yes
UL/CUL Listing	Yes

Dimensions

Height (in)	18.5
Width (in)	10.2
Depth (in)	10.9
Weight (lb)	28.0
Height (mm)	470
Width (mm)	258
Depth (mm)	279.1

Dimensions

Weight (kg)

12.7