

Alternate Catalog No. PSTX470-690-70
Catalog No. 1SFA898216R7000

Description: "PSTX470, 690V, 100-250VAC"

UPC No 7320500508985

Home > Drives and Soft Starters > Softstarter - Open (PSTX)



Representative Image

Descriptors

Category	Softstarter - Open (PSTX)
----------	---------------------------

Specifications

Product Type	Soft Starters
Input Voltage	208-690 V
Control Voltage	100-250 V
Normal Duty: Output Current (A)	480
Normal Duty: Motor Power (HP) at 208V	150
Normal Duty: Motor Power (HP) at 230V	200
Normal Duty: Motor Power (HP) at 460V	400
Normal Duty: Motor Power (HP) at 575V	500
Heavy Duty: Output Current (A)	361
Heavy Duty: Motor Power (HP) at 208V	125
Heavy Duty: Motor Power (HP) at 230V	150
Heavy Duty: Motor Power (HP) at 460V	300
Heavy Duty: Motor Power (HP) at 575V	350
Power Dissipation In Watts	99

Classifications

RoHS Indicator	Yes
UL/CUL Listing	Yes

Dimensions

Height (in)	19.4
Width (in)	14.2
Depth (in)	11.1
Weight (lb)	55.1
Height (mm)	493
Width (mm)	361
Depth (mm)	282.1

Dimensions

Weight (kg)

25