

**Alternate Catalog No. PSTX370-690-70**  
**Catalog No. 1SFA898215R7000**

**Description: "PSTX370, 690V, 100-250VAC"**

**UPC No 7320500501498**

**Home > Drives and Soft Starters > Softstarter - Open (PSTX)**



Representative Image

**Descriptors**

Category	Softstarter - Open (PSTX)
----------	---------------------------

**Specifications**

Product Type	Soft Starters
Input Voltage	208-690 V
Control Voltage	100-250 V
Normal Duty: Output Current (A)	361
Normal Duty: Motor Power (HP) at 208V	125
Normal Duty: Motor Power (HP) at 230V	150
Normal Duty: Motor Power (HP) at 460V	300
Normal Duty: Motor Power (HP) at 575V	350
Heavy Duty: Output Current (A)	302
Heavy Duty: Motor Power (HP) at 208V	100
Heavy Duty: Motor Power (HP) at 230V	100
Heavy Duty: Motor Power (HP) at 460V	250
Heavy Duty: Motor Power (HP) at 575V	300
Power Dissipation In Watts	148

**Classifications**

RoHS Indicator	Yes
UL/CUL Listing	Yes

**Dimensions**

Height (in)	18.5
Width (in)	10.2
Depth (in)	10.9
Weight (lb)	28.0
Height (mm)	470
Width (mm)	258
Depth (mm)	279.1

## Dimensions

Weight (kg)

12.7