

Project Name

Location

Prepared By



# SATCO S39718

25T5/LED/46-840/BP/HO/SE-DE

**Notes**

[www] 01-29-2021 11:42:03

**General**

Status	Active
Watts	25
Fluorescent Equivalent	54
Volts	120V-277V
Ballast Type	Type B
Shape	T5
Base	Miniature Bi Pin
ANSI Base	G5
Nominal Length	48
Finish	Frosted
CCT (Kelvin)	4000
Temperature	Cool White
CRI	83
Lumens	3300
Beam Spread	240
Dimmable	Non-Dimmable
Hours Rated	50000
Lamp Type	Linear
Technology	LED

**Electrical**

Operating Frequency	50/60Hz
Power Factor	0.9
THD	20%
Operating Temperature	-25C (-13F) to a maximum of +45C (+113F)

**Physical**

MOL	46
MOD	0.83
Material	Glass
Lens Finish	Frosted
Lens Material	Glass
Weight (lb.)	0.4

**Additional Information**

Shatter-Proof Type	PET Coated
Warranty	5 Year Limited - T5 LED Bulbs - Ballast Bypass

**Compliance**

Safety Listing	cULus Classified
Location Rating	Damp
Energy Star	No
DLC Approved	Yes
DLC ID	PLNRT1RABCIP
California Status	Lawful for sale in California
Nevada Status	Lawful for sale in Nevada
RoHS Compliant	Yes
FCC Compliant	Yes



NSF Approved

Yes

