

Project Name

Location

Prepared By



SATCO S39719

25T5/LED/46-850/BP/HO/SE-DE

Notes

[www] 01-29-2021 11:42:03

General

| | |
|------------------------|------------------|
| Status | Active |
| Watts | 25 |
| Fluorescent Equivalent | 54 |
| Volts | 120V-277V |
| Ballast Type | Type B |
| Shape | T5 |
| Base | Miniature Bi Pin |
| ANSI Base | G5 |
| Nominal Length | 48 |
| Finish | Frosted |
| CCT (Kelvin) | 5000 |
| Temperature | Natural Light |
| CRI | 83 |
| Lumens | 3400 |
| Beam Spread | 240 |
| Dimmable | Non-Dimmable |
| Hours Rated | 50000 |
| Lamp Type | Linear |
| Technology | LED |

Electrical

| | |
|-----------------------|--|
| Operating Frequency | 50/60Hz |
| Power Factor | 0.9 |
| THD | 20% |
| Operating Temperature | -25C (-13F) to a maximum of +45C (+113F) |

Physical

| | |
|---------------|---------|
| MOL | 46 |
| MOD | 0.83 |
| Material | Glass |
| Lens Finish | Frosted |
| Lens Material | Glass |
| Weight (lb.) | 0.4 |

Additional Information

| | |
|--------------------|--|
| Shatter-Proof Type | PET Coated |
| Warranty | 5 Year Limited - T5 LED Bulbs - Ballast Bypass |

Compliance

| | |
|-------------------|-------------------------------|
| Safety Listing | cULus Classified |
| Location Rating | Damp |
| Energy Star | No |
| DLC Approved | Yes |
| DLC ID | PLYF62HN8A9I |
| California Status | Lawful for sale in California |
| Nevada Status | Lawful for sale in Nevada |
| RoHS Compliant | Yes |
| FCC Compliant | Yes |



NSF Approved

Yes

