

Project Name

Location

Prepared By



SATCO S11433

8.5A19/LED/850/AGRI/120V/D

Notes

[www] 01-29-2021 11:42:01

General

Status	Active
Watts	8.5
Incandescent Equivalent	60-75
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	Frosted
CCT (Kelvin)	5000
Temperature	Natural Light
CRI	80
Lumens	1000
Beam Spread	140
Dimmable	Yes - Dimmable
Hours Rated	25000
Technology	LED

Electrical

Operating Frequency	60 Hz
Dimming Type	Triac
Power Factor	0.9
Operating Temperature	-20C (-4F) to a maximum of 45C (113F)

Physical

MOL	4.61
MOD	2.36
Housing Color	White
Weight (lb.)	0.11

Additional Information

Warranty	3 Year Limited - 10 hr per day
----------	--------------------------------

Compliance

Safety Listing	cULus Listed
Location Rating	Wet
Energy Star	No
California Status	Non-Compliant
RoHS Compliant	Yes
SDS Sheet	LED_Lamp