## SATCO' NUVO

Project Name

Location

Prepared By



**SATCO S29400** 

6.5PAR20/LED/25'/927/120V

Notes

General Status Active Watts 6.5 50 Incandescent Equivalent Fluorescent Equivalent 11.00 Volts 120V PAR20 Shape Base Medium ANSI Base E26 Finish Silver CCT (Kelvin) 2700 Temperature Warm White CRI 90 Lumens 520 Beam Spread 25 Dimmable Yes - Dimmable Hours Rated 25000 Lamp Type PAR Technology LED Electrical 60 Hz **Operating Frequency** CBCP 1179 Dimming Type Thyristor Power Factor 0.9 -20C (-4F) to a maximum of +45C **Operating Temperature** (+113F) Physical MOL 2.99 MOD 2.44 Lensed Lensed Lamp Lens Finish Clear Lens Material Thermo Plastic Housing Color Silver Weight (lb.) 0.10 Additional Information Rated For Enclosed Fixture Yes Warranty 3 Year Limited - 12 hr per day Compliance Safety Listing cULus Location Rating Wet Energy Star Yes ES Unique ID ESID-2366318 California Status California T24 Compliant Nevada Status Lawful for sale in Nevada **RoHS** Compliant Yes FCC Compliant Yes

For More Information Visit: <u>https://www.satco.com/</u>



SDS Sheet

Copyright 2020 Satco Products, Inc. All Rights Reserved

For More Information Visit: <u>https://www.satco.com/</u>

