SATCO" NUVO"

Project Name

Location

Prepared By



SATCO S29411

Notes

12.5PAR30/SN/LED/25'/930/120V

Status	Active
Watts	12.5
Incandescent Equivalent	75
Fluorescent Equivalent	15.00
Volts	120V
Shape	PAR30SN
Base	Medium
ANSI Base	E26
Finish	Silver
CCT (Kelvin)	3000
Temperature	Warm White
CRI	90
Lumens	1000
Beam Spread	25
Dimmable	Yes - Dimmable
Hours Rated	25000
Lamp Type	PAR
Technology	LED
Electrical	
Operating Frequency	60 Hz
CBCP	2910
Dimming Type	Thyristor
Power Factor	0.9
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)
Physical	
MOL	3.70
MOD	3.74
Lensed	Lensed Lamp
Lens Finish	Clear
Lens Material	Thermo Plastic
Housing Color	Silver
Additional Information	
Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited - 12 hr per day
Compliance	
Safety Listing	cULus
Location Rating	Wet
Energy Star	Yes
ES Unique ID	ESID-2366550
California Status	California T24 Compliant
Nevada Status	Lawful for sale in Nevada
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp

For More Information Visit: https://www.satco.com/



Copyright 2020 Satco Products, Inc. All Rights Reserved

For More Information Visit: <u>https://www.satco.com/</u>

