

Project Name

Location

Prepared By



Notes

[www] 01-29-2021 11:42:03

General

Status	Active
Watts	12.5
Incandescent Equivalent	75
Fluorescent Equivalent	15.00
Volts	120V
Shape	PAR30LN
Base	Medium
ANSI Base	E26
Finish	Silver
CCT (Kelvin)	2700
Temperature	Warm White
CRI	90
Lumens	1000
Beam Spread	25
Dimmable	Yes - Dimmable
Hours Rated	25000
Lamp Type	PAR
Technology	LED

Electrical

Operating Frequency	60 Hz
CBCP	2910
Dimming Type	Thyristor
Power Factor	0.9
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

Physical

MOL	4.57
MOD	3.74
Lensed	Lensed Lamp
Lens Finish	Clear
Lens Material	Thermo Plastic
Housing Color	Silver
Weight (lb.)	0.25

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited - 12 hr per day

Compliance

Safety Listing	cULus
Location Rating	Wet
Energy Star	Yes
ES Unique ID	ESID-2367051
California Status	California T24 Compliant
Nevada Status	Lawful for sale in Nevada
RoHS Compliant	Yes
FCC Compliant	Yes

