

## D7 Series General Purpose Plug-In Relay

D7PR31T

UPC:782114228333

### Dimensions:

- **Height:** 1.1 IN
- **Length:** 1.6 IN
- **Width:** 1.2 IN

**Weight:** .13 LB

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Coil Voltage:** 24V
- **Contact Configuration:** 3PDT
- **Contact Material:** Silver alloy
- **Contact Rating:** 15A
- **Cover:** Plain
- **Enclosure:** IP40
- **Indicator:** Optional LED
- **Maximum Voltage:** 300V switching
- **Options:** Mechanical flag indicator
- **Resistance:** 103 Ohms
- **Series:** D7 series
- **Terminals:** Plug-in

### Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [D7\\_R3 3D Model Xchange](#)
- [D7\\_R3 AutoCAD 2D Footprint \(mm\)](#)
- [D7\\_R3 AutoCAD 2D Footprint](#)
- [D7\\_R3 2D PDF](#)
- [D7\\_R3 3D Inventor](#)



- [D7\\_R3 2D Drawing Xchange](#)
- [Eaton Specification Sheet - D7PR31T](#)

**Certifications:**

- CSA file No. LR217069
- UL Listed file E65657
- cRUus
- UL Listed file E37317
- CSA file No. LR217017

**Product compliance:**

- RoHS Compliant
- CE Marked