

D2 Series General Purpose Plug-In Relay

D2PF2AT

UPC:782116484508

Dimensions:

- **Height:** 1.1 IN
- **Length:** 1.54 IN
- **Width:** .83 IN

Weight:.05 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Coil Voltage:** 24V
- **Contact Configuration:** DPDT
- **Contact Material:** Silver alloy
- **Contact Rating:** 10A
- **Cover:** Full featured
- **Enclosure:** IP40
- **Maximum Voltage:** 300V switching
- **Options:** Locking pushbutton, bipolar LED, removable ID tag, mechanical flag indicator
- **Resistance:** 180 Ohms
- **Series:** D2 series
- **Terminals:** Plug-in

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [D2_F2 AutoCAD 2D Footprint](#)
- [D2_F2 3D Model Xchange](#)
- [D2_F2 2D PDF](#)
- [D2_F2 3D Inventor](#)
- [D2_F2 2D Drawing Xchange](#)



- [D2_F2 AutoCAD 2D Footprint \(mm\)](#)
- [Eaton Specification Sheet - D2PF2AT](#)

Certifications:

- UL Listed
- CSA Certified
- cRUus

Product compliance:

- RoHS Compliant
- CE Marked