

Project Name

Location

Prepared By



**Notes**

[www] 02-09-2021 10:35:55

**General**

Status	Active
Watts	12.5
Incandescent Equivalent	75
Fluorescent Equivalent	15.00
Volts	120V
Shape	PAR30LN
Base	Medium
ANSI Base	E26
Finish	Silver
CCT (Kelvin)	2700
Temperature	Warm White
CRI	90
Lumens	1000
Beam Spread	40
Dimmable	Yes - Dimmable
Hours Rated	25000
Lamp Type	PAR
Technology	LED

**Electrical**

Operating Frequency	60 Hz
CBCP	1315
Dimming Type	Thyristor
Power Factor	0.9
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

**Physical**

MOL	4.57
MOD	3.74
Lensed	Lensed Lamp
Lens Finish	Clear
Lens Material	Thermo Plastic
Housing Color	Silver
Weight (lb.)	0.25

**Additional Information**

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited - 12 hr per day

**Compliance**

Safety Listing	cULus
Location Rating	Wet
Energy Star	Yes
ES Unique ID	ESID-2367149
California Status	California T24 Listed
Nevada Status	Lawful for sale in Nevada
RoHS Compliant	Yes
FCC Compliant	Yes



