SATCO' NUVO

Project Name

Location

Prepared By



SATCO S29433

12.5PAR30/LN/LED/40'/940/120V

Notes

General Status Active Watts 12.5 75 Incandescent Equivalent Fluorescent Equivalent 15.00 Volts 120V PAR30LN Shape Base Medium ANSI Base E26 Finish Silver CCT (Kelvin) 4000 Temperature Cool White CRI 90 1000 Lumens Beam Spread 40 Dimmable Yes - Dimmable Hours Rated 25000 Lamp Type PAR Technology LED Electrical 60 Hz **Operating Frequency** CBCP 1315 Dimming Type Thyristor Power Factor 0.9 -20C (-4F) to a maximum of +45C **Operating Temperature** (+113F) Physical MOL 4.57 MOD 3.74 Lensed Lensed Lamp Lens Finish Clear Lens Material Thermo Plastic Housing Color Silver 0.25 Weight (lb.) Additional Information Rated For Enclosed Fixture Yes Warranty 3 Year Limited - 12 hr per day Compliance Safety Listing cULus Location Rating Wet Energy Star Yes ESID-2367153 ES Unique ID California T24 Listed California Status Nevada Status Lawful for sale in Nevada **RoHS** Compliant Yes FCC Compliant Yes

Copyright 2020 Satco Products, Inc. All Rights Reserved For More Information Visit: <u>https://www.satco.com/</u>



SDS Sheet

Copyright 2020 Satco Products, Inc. All Rights Reserved

For More Information Visit: <u>https://www.satco.com/</u>

