

Project Name

Location

Prepared By



**Notes**

[www] 02-09-2021 10:35:55

**General**

Status	Active
Watts	15
Incandescent Equivalent	90
Fluorescent Equivalent	23.00
Volts	120V
Shape	PAR38
Base	Medium
ANSI Base	E26
Finish	Silver
CCT (Kelvin)	4000
Temperature	Cool White
CRI	90
Lumens	1200
Beam Spread	25
Dimmable	Yes - Dimmable
Hours Rated	25000
Lamp Type	PAR
Technology	LED

**Electrical**

Operating Frequency	60 Hz
CBCP	3698
Dimming Type	Thyristor
Power Factor	0.9
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

**Physical**

MOL	5.00
MOD	4.72
Lensed	Lensed Lamp
Lens Finish	Clear
Lens Material	Thermo Plastic
Housing Color	Silver
Weight (lb.)	0.34

**Additional Information**

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited - 12 hr per day

**Compliance**

Safety Listing	cULus
Location Rating	Wet
Energy Star	Yes
ES Unique ID	ESID-2367498
California Status	California T24 Listed
Nevada Status	Lawful for sale in Nevada
RoHS Compliant	Yes
FCC Compliant	Yes

