

Round retrofit LED panel light

The aluminum retrofit LED panel offers the easiest and most practical solution to your existing lighting needs. For style and convenience, the removable outer trim attaches with magnetic fasteners to create a seamless look. Can be easily retrofitted in existing 4" canisters or standard octagonal junction boxes.



WET



COLOR TEMPERATURE

SWITCH*



RETROFIT



*Model RTF4-CC only

Model	Size	Watts	Delivered lumens	LED lumens	CRI	Color °T	Voltage
RTF4-3K	4"	9 W	550 lm	630 lm	90	3000 K	120 V
RTF4-CC	4"	9 W	500 lm	580 lm	90	2700, 3000, 3500, 4000, 5000 K	120 V

Specifications

Fits on octagonal junction boxes
Includes A-19 socket
Fits into 4" recessed housings
Minimal heat emission
Aluminum construction
Switch-selectable CCT:
2700K/ 3000K/ 3500K/ 4000K/ 5000K
(model RTF4-CC only)
Over 50,000 hours of service life
Magnetic trim finish
Suitable for wet locations
Refer to website for dimmer
compatibility
Ideal operating temperature:
-20° to 40° C
5-year warranty

Finish

- **BK** Black (RTF4-3K)
- **SN** Satin Nickel (RTF4-3K)
- **WH** White (RTF4-3K, (RTF4-CC))

Order example

RTF4-3K-BK
Black 4" retrofit panel light with
550 Lumens at 3000 K

Note

Other Color °T and Finishes available,
but may require MOQ's and longer
lead times. Please contact your DALI
representative for more information.

RTF4-3K

