

Coaxial Termination Products

Universal Compression Connectors

- Four universal connectors terminate all plenum RG-6, RG-6, RG-59 and RG-11 braid types from 60% through quad shielding
- One connector for all cable types within a given RG series
- Approved by most satellite and cable TV companies
- Approved for indoor/outdoor use



Description	Qty.	Cat. No.
Universal RG-59 Compression Connectors	Jar of 50	89-059
	Jar of 100	89-159
Universal RG-6 Compression Connectors	Jar of 50	89-060
	Jar of 100	89-160
Plenum RG-6 Compression Connectors	Jar of 50	89-060P
	Jar of 100	89-160P
Universal RG-11 Compression Connectors	Clam of 10	89-011

CMP Compression Connectors

- Approved for use by most cable TV and satellite companies
- RF signal containment ensures strong signal
- Permanent connections do not pull off or come loose
- One-piece design for quick installation
- Compression port seal provides a water-tight seal for outdoor applications



Description	Qty.	Cat. No.
RG-59 Compression F-Connector	50	89-054
RG-59 Compression F-Connector	100	89-104
RG-6 Compression F-Connector	4	89-015
RG-6 Compression F-Connector	10	89-035
RG-6 Compression F-Connector	50	89-055
RG-6 Compression F-Connector	100	89-105
RG-6 Quad Compression F-Connector	4	89-016
RG-6 Quad Compression F-Connector	50	89-056
RG-6 Quad Compression F-Connector	100	89-106

Compression F-Connector Port Seals

- For use with IDEAL RG-6, RG-6 Quad and RG-59 F-Style compression connectors to make connections water tight



Description	Qty.	Cat. No.
Port Seals	5	89-026

BNC Compression Connectors

- Color coded by cable series for easy identification
- Approved for indoor/outdoor use



Description	Qty.	Cat. No.
BNC RG-6 Compression Connector	Clam of 15	89-057
BNC RG-6 Compression Connector	Jar of 50	89-5057
BNC RG-59 Compression Connector	Clam of 15	89-058
BNC RG-59 Compression Connector	Jar of 50	89-5058

Mini Compression Connectors

- For use with most 21-25 AWG mini coax cable
- Body is nickel plated for outstanding corrosion resistance
- Mini RCA head is gold plated for superior contact performance
- Bandwidth is 5 MHz - 3 GHz, Impedance is 75 Ohms (nominal), return loss min. -30 dB @ 3 GHz



F-Connector

RCA Connector

Description	Qty.	Cat. No.
Mini Compression F-Connector	10	89-014SM
Mini Compression RCA Connector	10	89-014SMRCA

Push-on F-Connectors

- Permanent connection
- No termination tool needed



Description	Qty.	Cat. No.
RG-6 Push-on F-Connectors	4	85-065
RG-6Q Push-on F-Connectors	4	85-066
RG-59 Push-on F-Connectors	4	85-067
RG-6 Push-on F-Connectors	50	89-165
Coax Connector Kit w/Economy Coax Stripper & four RG-6 Push-On F-Connectors	—	33-320

Coax Connector Tool - F & BNC

- Works on compression and hex connectors
- Makes attaching (and detaching) connector to equipment easier
- Aids in installing CATV connectors on coax cable
- New comfort grip handle



Description	Cat. No.
Coax Connector Tool - F & BNC — 8 in. overall (3 in. blade)	35-046