

Eaton M22 modular pushbutton

M22-DLH-R-K11-R

UPC:786685274935

Dimensions:

- **Height:** 3.45 IN
- **Length:** 1.46 IN
- **Width:** 1.18 IN

Weight:.085 LB

Notes:Positively driven contact blocks.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Application:** Pushbutton
- **Special Features:** M22 series
- **Type:** 22.5 mm Modular
- **Action:** Momentary
- **Actuator:** Button, Extended
- **Bezel:** Silver
- **Button Color:** Red
- **Contact Configuration:** 1NO-1NC
- **Environmental Rating:** IP67, IP69K, NEMA 4X, 13
- **Illumination:** Illuminated
- **Size:** 22.5 mm
- **Series:** M22
- **Voltage Rating:** 12-30 Vac/dc

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [M22 Operators and Accessories](#)
- [M22 Pilot Devices](#)



- [Eaton Specification Sheet - M22-DLH-R-K11-R](#)

Certifications:

- CSA Certified
- CCC Marked
- Lloyd's Register Certified

Product compliance:

- GoST-R
- CE Marked
- Bureau Veritas