

Project Name

Location

Prepared By



Notes

[www] 01-19-2021 00:51:05

General

Status	Active
Watts	14
Fluorescent Equivalent	32W/30W/28W/25W
Volts	120V-270V
Ballast Type	Type A
Shape	T8
Base	Medium Bi Pin
ANSI Base	G13
Nominal Length	48
Finish	Gloss White
CCT (Kelvin)	3000
Temperature	Warm White
CRI	82
Lumens	2200
Beam Spread	210
Dimmable	Check Ballast MFG for Dimmer Compatibility
Hours Rated	50000
Lamp Type	Linear
Technology	LED

Electrical

Operating Frequency	50/60 Hz
Power Factor	0.9
THD	20%
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

Physical

MOL	48
MOD	1.1
Material	Glass
Lens Finish	Frosted
Lens Material	Glass
Housing Color	White
Weight (lb.)	0.44

Additional Information

Warranty	5 Year Limited - T8 LED Bulbs
----------	-------------------------------

Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	No
DLC Approved	Yes
DLC ID	PLC0C6BUPVBV
California Status	Lawful for sale in California
Nevada Status	Lawful for sale in Nevada
RoHS Compliant	Yes
FCC Compliant	Yes

NSF Approved

Yes

