

PROJECT:	DATE:
TYPE:	NOTES:

HR SERIES - FLOOD LIGHTING

TMULTI-USE WEATHERPROOF



HR-1 (Full-Cup Holder and Cover)



HR-2 (Twin Full-Cup Holders and Cover)



HR (Full-Cup Holder Only)

CONSTRUCTION

- Rugged die-cast aluminum full cup holder aluminum floodlight fixture.
- Mounts to standard junction box covers, includes silicone gasket.
- Standard finish is grey. Available options include black, white or bronze powder coat paint finish.

FEATURES

- Available as single or twin floodlight or as kit including cover.
- Fully adjustable with serrated teeth for locking in place. 1/2" NPS threaded arm with locking nut.
- Medium base porcelain socket for Par38 lamp (150 Watt incandescent max).
- Lamp options include incandescent, CFL or LED. (Lamp not included.)
- Water resistant glass lens kit available with fixture - see HRL.

ALSO AVAILABLE IN:

White

Black

Bronze

APPLICATION:

in Ideal for lighting perimeters


- For use outdooors


CERTIFICATION:






DIMENSIONS







ORDER INFO

STOCK CODE / DESCRIPTION	STOCK CODE / DESCRIPTION
008311 HR - GREY FLOODLIGHT	094419 HRR-1 - BRONZE FLOODLIGHT & COVER
008319 HRB - BLACK FLOODLIGHT	008334 HRW-1 - WHITE FLOODLIGHT & COVER
008330 HRR - BRONZE FLOODLIGHT	094414 HR-2 -GREYTWIN FLOODLIGHT
094420 HRW - WHITE FLOODLIGHT	008322 HRB-2 - BLACK TWIN FLOODLIGHT & COVER
094413 HR-1 - GREY FLOODLIGHT & COVER	008332 HRR-2 - BRONZE TWIN FLOODLIGHT & COVER
008320 HRB-1 - BLACK FLOODLIGHT & COVER	094421 HRW-2 - WHITE TWIN FLOODLIGHT & COVER