Flat Gimbal









When searching for lighting flexibility, look no further than our 4" flat gimbal LED downlight. With a powerful lumen output and the ability to shine your light on a 360 degree rotation and a 90° tilt angle, this product will meet your every needs.



Model	Size	Watts	Delivered lumens	LED lumens	CRI	Color °T	Voltage
FGM4-3K	4"	9 W	700 lm	850 lm	90	3000 K	120 V

Specifications

Every fixture includes a junction box with integrated dimmable driver
Can be daisy chained
Superior LED performance and lifespan
90° tilting, 360° rotation
Minimal heat emission
Aluminum construction
Low profile

40° beam spread IC certification (suitable for direct contact with insulation) Air-tight certified as per ASTM E283-04 Suitable for damp locations

Finish

BK Black

SN Satin Nickel
WH White

Accessories

RFP-UNI

Universal rough-in plate

RFP-46

Rough-in plate for 4" and 6" models

Order example

FGM4-3K-BK

4" flat gimbal recessed downlight with 700 Lumens at 3000 K in a black finish

Note

Other Color °T and Finishes available, but may require MOQ's and longer lead times. Please contact your DALS representative for more information.

