

Project Name

Location

Prepared By



**Notes**

[www] 10-12-2020 05:26:19

**General**

Status	Discontinued
Finish	White
Wattage	13.5
Style	Utility
CCT (Kelvin)	3000
Color Temperature	Warm White
Length (in.)	7.63
Width (in.)	7.63
Height (in.)	3.75
Indoor or Outdoor Fixture	Indoor

**Specifications**

Technology	LED
CRI	90+
Lumen Output	820
Rated Hours	50000
Voltage	120V
Dimmable	Yes - Dimmable
Fixture Type	Flush Mount

**Compliance**

Safety Listing	cETLus
Location Rating	Damp
UL Application	Ceiling
Energy Star	No
CA Prop 65	Lead
RoHS Compliant	Yes

**Additional Information**

Warranty	5 Year Limited - Fixtures
----------	---------------------------