



CA-750

by CMC
Catalog ID: CA-750

TYPE: CA / LI, Dual-Rated Solderless Connectors, For use with both aluminum and copper conductors, Cond. Range: 750 kcmil - 3/0 AWG / (2) 250 kcmil -1/0 AWG. CSA Certified. CMC® Rectangular connectors are manufactured from high strength 6061-T6 aluminum alloy to insure both maximum strength and conductivity. They are dual rated for both copper and aluminum conductors and are electro tin plated to provide low contact resistance and protection against corrosion. Assembly can be made with only a screwdriver or allen wrench and the connectors are reusable.

Product Details

General

Material	Aluminum
Type	Bolted Lugs & Terminals
UPC	192663053865

Dimensions

Height	2.06 in
Length	1.25 in
Width	1.38 in

Conductor Related

Conductor - Copper Str Size Range	750 Kcmil-3/0 AWG / (2) 250 Kcmil-1/0 AWG
-----------------------------------	---