


18 AWG 5/C Armoured Shielded Fire Alarm Cable FT4

 componetics.com/product/344-0518/



SKU: 344-0518 Category: [Fire Alarm Cables](#) Tags: [18 AWG 5/C](#), [Armoured Fire Alarm](#), [CSA FT4](#), [FAS 105](#), [Shielded](#), [Solid Bare Copper](#)

Applications

Fire protective signaling circuits, Smoke detectors, Strobes/Sirens, Pull stations voice communications, Burglar alarms, Audio, Control, Initiating and notification circuits, Microprocessor/Addressable controlled systems

Features & Benefits

- Install friendly
- Tested physically and electrically in accordance with CSA standards
- Sunlight Resistant & RoHS Compliant
- Free from restricted materials and hazardous compounds

SKU: 344-0518 Category: [Fire Alarm Cables](#) Tags: [18 AWG 5/C](#), [Armoured Fire Alarm](#), [CSA FT4](#), [FAS 105](#), [Shielded](#), [Solid Bare Copper](#)

Description

Product Specification

- **Conductor:** Solid Bare Conductor
- **Number of Conductors:** 5
- **Size:** 18 AWG
- **Shielding:** 100% Aluminum Foil Shield
- **Armour:** Red Dyed Aluminum Interlocked Armour (AIA)
- **Insulation:** PVC
- **Conductor Color Code:** Black/Red/Green/Blue/Brown

- **Rip Cord:** None
- **Jacket:** PVC
- **Nominal Cable Diameter:** 0.450"
- **Nominal Cable Net Weight (lbs/500'):** 55
- **Temperature Rating:** -20 C to 105 C
- **Voltage:** 300v
- **Standards:** CSA FT4 C22.2 No. 208.03