

ES137S

1 3/8" ELECTRICAL SPLICE KIT

UPC: 085937079480

Country of Origin:

UNSPSC: 39121718

USA

Commodity: Cable splicing kits



"SHAKE N SEAL" electrical splice kits offer absolute protection for any splice (up to 600V) in a wet or damp environment.

Product Attributes

Brand Name	Minerallac Company
Sub Brand	Uruseal [®]
Type	Shake N' Seal [®] Electrical Splice Kit
Special Features	1-3/8" Permanent Splice Protection
Application	Butt or Branch Splice, Direct Burial, Water Tight
Standard	CSA [®] LR204840, UL [®] 31YB
Cable Type	Single or Multi-Conductor Wire
Number Of Cables	18-16AWG-20, 14-12AWG-12, 10AWG-8, 8AWG-6, 6AWG-4, 4AWG-2, 3AWG-2, 2AWG-1, 1AWG-1
Cable Size	18-1 AWG
Voltage Rating	600 Volts or Less
Color	Black
Insulation	Permanent Encapsulant
Operating Temperature	Max 90° C

Item Status: Active
Standard Qty: 1

Minerallac Company

Tel: 800-927-3293
Fax: 800-824-8942
www.minerallac.com