



Core HD Cameras	C133ED	C134ED	C133BD	C134BD	NEW	C243EW2	NEW	C247EW2
	Mini IR Eyeball Dome	Varifocal IR Eyeball Dome	Mini IR Bullet	Varifocal IR Bullet		Mini IR Eyeball Dome		Motorized VF IR Eyeball Dome
<b>Resolution</b>	HD 2.1MP	HD 2.1MP	HD 2.1MP	HD 2.1MP		HD 2.1MP / 960H		HD 2.1MP / 960H
<b>Image Sensor</b>	1/2.7" CMOS	1/2.7" CMOS	1/2.7" CMOS	1/2.7" CMOS		1/2.9" CMOS		1/2.9" CMOS
<b>True WDR</b>	-	-	-	-		Yes / ≤ 100dB		Yes / ≤ 100dB
<b>Focal Length / FOV (H)</b>	3.6mm / 80°	2.8 - 12mm / 80° ~ 30°	3.6mm / 80°	2.8 - 12mm / 80° ~ 30°		2.8mm / 105°		2.8-12mm / 102° ~ 30°
<b>Infrared Nightvision Range</b>	70ft / 21m	90ft / 27m	70ft / 21m	90ft / 27m		82ft / 25m		100ft / 31m
<b>Video Output</b>	MPX 1080p	MPX 1080p	MPX 1080p	MPX 1080p		Dual BNC - Multi-Format 1080p / 960H		Dual BNC - Multi-Format 1080p / 960H
<b>OSD</b>	Yes	Yes	Yes	Yes		Yes		Yes
<b>IP Rating / Min. Oper. Temp.</b>	IP66 / -22°F/-30°C	IP66 / -22°F/-30°C	IP66 / -22°F/-30°C	IP66 / -22°F/-30°C		IP66 / -22°F/-30°C		IP66 / -22°F/-30°C
<b>Power</b>	12V DC	12V DC	12V DC	12V DC		12V DC		12V DC / 24V AC
<b>Warranty Period</b>	3 Years							



Core HD Cameras	NEW	C243MT2	NEW	C347VC2	NEW	C243BW2	C237BD1	NEW	C347BC2	C336ZC1
		Micro IR Audio Vandal Dome		Motorized VF IR CNV™ Vandal Dome		Mini IR Bullet	Motorized VF IR Bullet		Motorized VF IR CNV™ Bullet	4" PTZ Speed Dome
<b>Resolution</b>		HD 2.1MP		HD 2.1MP / 960H		HD 2.1MP / 960H	HD 2.1MP / 960H		HD 2.1MP / 960H	HD 1MP
<b>Image Sensor</b>		1/2.8" CMOS		1/2.8" CMOS		1/2.9" CMOS	1/2.8" CMOS		1/2.8" CMOS	1/3" CMOS
<b>True WDR</b>		-		Yes / ≤ 100dB		Yes / ≤ 100dB	Yes / ≤ 100dB		Yes / ≤ 100dB	-
<b>Focal Length / FOV (H)</b>		2.8mm / 90°		2.8 - 12mm / 103° - 31°		2.8mm / 105°	6 - 22mm / 36° - 17°		2.8 - 12mm / 103° - 31°	12x Optical / 5.1 - 61mm / 51° - 4°
<b>Infrared Nightvision Range</b>		60ft / 18m		115ft / 35m		82ft / 25m	115ft / 35m		115ft / 35m	-
<b>Video Output</b>		MPX 1080p		Dual BNC - Multi-Format 1080p / 960H		Dual BNC - Multi-Format 1080p / 960H	Dual BNC - MPX 1080p / 960H		Dual BNC - Multi-Format 1080p / 960H	MPX 720p
<b>OSD</b>		Yes		Yes		Yes	Yes		Yes	Yes
<b>IP/Vandal Rating / Min. Oper.</b>		IP67 / IK10 / -22°F/-30°C		IP66 / IK10 / -22°F/-30°C		IP66 / -22°F/-30°C	IP66 / -22°F/-30°C		IP66 / -22°F/-30°C	IP66 / -40°F/-40°C
<b>Power</b>		12V DC		12V DC / 24V AC		12V DC	12V DC / 24V AC		12V DC / 24V AC	24V AC
<b>Warranty Period</b>		3 Years								