

Features:

- High power handling 8" in-ceiling speaker system
- New trim-less magnetic grille
- Smooth-wide frequency response
- 8 inch Polypropylene woofer cone
- Rubber woofer surround
- 30 oz ferrite woofer magnet
- 1 inch aim-able silk dome tweeter
- Neodymium tweeter magnet
- High quality crossover with air core inductors
- PTZ tweeter protection with automatic reset
- 4 heavy duty mounting clamps.
- Gold plated 12awg binding posts
- Complete rough in brackets included (RI-875)
- Paint-able to match any decor
- Sold as pairs
- Master carton 1 pair
- 10 year warranty



Specifications:

- Diameter Woofer 8" (203.2mm) Polypropylene
- Diameter Tweeter 1" (25.4mm) silk dome aim-able
- Power Handling 150 watts (peak)
- Impedance 8 ohms (nominal)
- Frequency Response 45Hz - 22kHz (± 10 dB)
- Dispersion 110 °
- Sensitivity 92dB (1W 1M) Average

Included:

- RI-875 rough-in brackets (pair)
- Cutout template
- Paint shield
- Installation manual



Dimensions:

- Dimensions Overall 10.875" (277mm)
- Cutout Dimensions Speaker 9.9" (250mm)
- Cutout Dimensions RI Bracket 10.125" (251mm)
- Depth 4.25" (107.95mm)
- Shipping Weight 16.lbs (7.25kg) per pair
- Shipping Weight master carton 1 pair 16.Lbs

Optional Square Magnetic Grille

Includes RI Brackets



SG-K8-TL

