

## ST-456 TWIN TURBO NOZZLE LANCES

**5070 PSI**

*The increased tearing action of the rotating spray is ideal for hard surface applications, such as concrete graffiti cleaning or caked mud on heavy equipment.*

| ORDER #   | PRESSURE | TEMP.  | LENGTH | INLET    | ORIFICE | WEIGHT | NOZZLE REPAIR KIT |
|-----------|----------|--------|--------|----------|---------|--------|-------------------|
| 999456530 | 5070 PSI | 200° F | 42 in  | 1/4" MPT | 2 x 3.0 | 3.2 lb | 200456130         |
| 999456535 | 5070 PSI | 200° F | 42 in  | 1/4" MPT | 2 x 3.5 | 3.2 lb | 200456135         |
| 999456540 | 5070 PSI | 200° F | 42 in  | 1/4" MPT | 2 x 4.0 | 3.2 lb | 200456140         |
| 999456545 | 5070 PSI | 200° F | 42 in  | 1/4" MPT | 2 x 4.5 | 3.2 lb | 200456145         |
| 999456550 | 5070 PSI | 200° F | 42 in  | 1/4" MPT | 2 x 5.0 | 3.2 lb | 200456150         |
| 999456555 | 5070 PSI | 200° F | 42 in  | 1/4" MPT | 2 x 5.5 | 3.2 lb | 200456155         |
| 999456560 | 5070 PSI | 200° F | 42 in  | 1/4" MPT | 2 x 6.0 | 3.2 lb | 200456160         |
| 999456570 | 5070 PSI | 200° F | 42 in  | 1/4" MPT | 2 x 7.0 | 3.2 lb | 200456170         |
| 999456580 | 5070 PSI | 200° F | 42 in  | 1/4" MPT | 2 x 8.0 | 3.2 lb | 200456180         |

- Increases cleaning efficiency by as much as 375%
- The 0° rotation creates a cleaning and tearing action
- The two turbo nozzles cover twice the amount of surface are resulting in saving time and money



**\* Lances not sold separately**

## ST-457 TWIN TURBO NOZZLE LANCES

**6000 PSI**

*The increased tearing action of the rotating spray is ideal for hard surface applications, such as concrete graffiti cleaning or caked mud on heavy equipment.*

| ORDER #   | PRESSURE | TEMP.  | LENGTH | INLET    | ORIFICE  | WEIGHT  | NOZZLE REPAIR KIT |
|-----------|----------|--------|--------|----------|----------|---------|-------------------|
| 999457530 | 6000 PSI | 212° F | 42 in  | 1/4" MPT | 2 x 3.0  | 4.28 lb | 200457130         |
| 999457535 | 6000 PSI | 212° F | 42 in  | 1/4" MPT | 2 x 3.5  | 4.28 lb | 200457135         |
| 999457540 | 6000 PSI | 212° F | 42 in  | 1/4" MPT | 2 x 4.0  | 4.28 lb | 200457140         |
| 999457545 | 6000 PSI | 212° F | 42 in  | 1/4" MPT | 2 x 4.5  | 4.28 lb | 200457145         |
| 999457550 | 6000 PSI | 212° F | 42 in  | 1/4" MPT | 2 x 5.0  | 4.28 lb | 200457150         |
| 999457555 | 6000 PSI | 212° F | 42 in  | 1/4" MPT | 2 x 5.5  | 4.28 lb | 200457155         |
| 999457560 | 6000 PSI | 212° F | 42 in  | 1/4" MPT | 2 x 6.0  | 4.28 lb | 200457160         |
| 999457570 | 6000 PSI | 212° F | 42 in  | 1/4" MPT | 2 x 7.0  | 4.28 lb | 200457170         |
| 999457580 | 6000 PSI | 212° F | 42 in  | 1/4" MPT | 2 x 8.0  | 4.28 lb | 200457180         |
| 999457590 | 6000 PSI | 212° F | 42 in  | 1/4" MPT | 2 x 9.0  | 4.28 lb | 200457190         |
| 999457510 | 6000 PSI | 212° F | 42 in  | 1/4" MPT | 2 x 10.0 | 4.28 lb | 200457110         |

- Increases cleaning efficiency by as much as 375%
- The 0° rotation creates a cleaning and tearing action
- The two turbo nozzles cover twice the amount of surface are resulting in saving time and money



**\* Lances not sold separately**