

# PORTABLE GENERATOR SPECIFICATIONS

Series	GP1800	GP3250	GP3250	GP5000	GP5000	GP5000	GP5500	GP5500	GP5500	GP6500
Model #	5723-1	5724-1	5789-0	5622-0	5698-0	5688-0	5736-0	5737-0	5738-0	5623-0
Emission Configuration	49 State/CSA	49 State/CSA	CARB	49-State	CARB	CSA	49-State	CARB	CSA	49-State
Running Watts	1800	3250	3250	5000	5000	5000	5500	5500	5500	6500
Starting Watts	2050	3750	3750	6250	6250	6250	6875	6875	6875	8000
Enging Size and Type	163cc OHV	206cc OHV	206CC OHV	389CC OHV	389CC OHV	389CC OHV	389CC OHV	389CC OHV	389CC OHV	389cc OHV
Starting Method	Manual	Manual	Manual	Manual	Manual	Manual	Manual	Manual	Manual	Manual
Battery	n/a	n/a	n/a	n/a	n/a	n/a	n/a	n/a	n/a	n/a
Outlets	(2) 5-20R 120V	(4) 5-20R 120V	(4) 5-20R 120V GFCI	(4) 5-20R 120V (1) L14-30R Twist-Lock 120/240V	(4) 5-20R 120V GFCI (1) L14-30R Twist-Lock 120/240V	(4) 5-20R 120V (1) L14-30R Twist-Lock 120/240V	(4) 5-20R 120V (1) L14-30R Twist-Lock 120/240V	(4) 5-20R 120V GFCI (1) L14-30R Twist-Lock 120/240V	(4) 5-20R 120V (1) L14-30R Twist-Lock 120/240V	(4) 5-20R 120V (1) L14-30R Twist-Lock 120/240V
Low Oil Shutdown	Low Level	Low Level	Low Level	Low Level	Low Level	Low Level	Low Level	Low Level	Low Level	Low Level
Hour Meter with Maintenance Resets	N/A	N/A	N/A	On Panel	On Panel	On Panel	On Panel	On Panel	On Panel	On Panel
Fuel Tank Construction	Steel, 4.0 Gal	Steel, 4.0 Gal	Steel, 4.0 Gal	Steel, 6.6 Gal	Steel, 6.6 Gal	Steel, 6.6 Gal	Steel, 6.6 Gal	Steel, 6.6 Gal	Steel, 6.6 Gal	Steel, 6.6 Gal
Run Time at 50%	14.5 Hours	12.5 Hours	12.5 Hours	10 Hours	10 Hours	10 Hours	10 Hours	10 Hours	10 Hours	10 Hours
Handles	n/a	Folding	Folding	Fold/Locking	Fold/Locking	Fold/Locking	Fold/Locking	Fold/Locking	Fold/Locking	Fold/Locking
Wheels	n/a	7" Solid Wheels	7" Solid Wheels	9.5" Solid Wheels	9.5" Solid Wheels	9.5" Solid Wheels	9.5" Solid Wheels	9.5" Solid Wheels	9.5" Solid Wheels	9.5" Solid Wheels
Warranty	2 Year Residential 1 Year Commercial	2 Year Residential 1 Year Commercial	2 Year Residential 1 Year Commercial	2 Year Residential 1 Year Commercial	2 Year Residential 1 Year Commercial	2 Year Residential 1 Year Commercial	2 Year Residential 1 Year Commercial	2 Year Residential 1 Year Commercial	2 Year Residential 1 Year Commercial	2 Year Residential 1 Year Commercial
Dimensions (L" x W" x H")	23.5 x 17 x 17.5	25 x 21 x 19.5	25 x 21 x 19.5	33.5 x 26.5 x 27	33.5 x 26.5 x 27	33.5 x 26.5 x 27	33.5 x 26.5 x 27	33.5 x 26.5 x 27	33.5 x 26.5 x 27	33.5 x 26.5 x 27
Unit Weight (lbs)	79	91	91	167	167	167	167	167	167	172

Series	GP6500	GP6500	GP7000	GP7000	GP7000E	GP8000	GP8000E	GP8000E	GP15000E	GP17500E
Model #	5690-0	5700-0	5625-0	5693-0	5626-0	5680-0	5681-0	5696-0	5734-0	5735-0
Emission Configuration	CSA	CARB	49-State	CSA	49-State	49-State	49-State	CSA	49-State	49-State
Running Watts	6500	6500	7000	7000	7000	8000	8000	8000	15000	17500
Starting Watts	8000	8000	8750	8750	8750	10000	10000	10000	22500	26250
Enging Size and Type	389cc OHV	389cc OHV	Generac 410cc OHVI	Generac 410cc OHVI	Generac 410cc OHVI	Generac 410cc OHVI	Generac 410cc OHVI	Generac 410cc OHVI	Generac 992cc OHVI	Generac 992cc OHVI
Starting Method	Manual	Manual	Manual	Manual	Electric/Manual	Manual	Electric/Manual	Electric/Manual	Electric	Electric
Battery	n/a	n/a	n/a	n/a	Included	n/a	Included	Included	Included	Included
Outlets	(4) 5-20R 120V (1) L14-30R Twist-Lock 120/240V	(4) 5-20R 120V GFCI (1) L14-30R Twist-Lock 120/240V	(4) 5-20R 120V (1) L14-30R Twist-Lock 120/240V	(4) 5-20R 120V (1) L14-30R Twist-Lock 120/240V	(4) 5-20R 120V (1) L14-30R Twist-Lock 120/240V	(4) 5-20R 120V (1) L14-30R Twist-Lock 120/240V	(4) 5-20R 120V (1) L14-30R Twist-Lock 120/240V	(4) 5-20R 120V (1) L14-30R Twist-Lock 120/240V	(2) 5-20R 120V (2) 5-20R GFCI (2) L5-30R (1) 14-30R (1) 14X50R (1) 12VDC	(2) 5-20R 120V (2) 5-20R GFCI (2) L5-30R (1) 14-30R (1) 14X50R (1) 12VDC
Low Oil Shutdown	Low Level	Low Level	Low Pressure	Low Pressure	Low Pressure	Low Pressure	Low Pressure	Low Pressure	Low Pressure	Low Pressure
Hour Meter with Maintenance Resets	On Panel	On Panel	On Panel	On Panel	On Panel	On Panel	On Panel	On Panel	On Panel	On Panel
Fuel Tank Construction	Steel, 6.6 Gal	Steel, 6.6 Gal	Steel, 8.0 Gal	Steel, 8.0 Gal	Steel, 8.0 Gal	Steel, 8.0 Gal	Steel, 8.0 Gal	Steel, 8.0 Gal	Resin, 16.0 Gal	Resin, 16.0 Gal
Run Time at 50%	10 Hours	10 Hours	11 Hours	11 Hours	11 Hours	11 Hours	11 Hours	11 Hours	10 Hours	10 Hours
Handles	Fold/Locking	Fold/Locking	Fold/Locking	Fold/Locking	Fold/Locking	Fold/Locking	Fold/Locking	Fold/Locking	Fixed, D-Style	Fixed, D-Style
Wheels	9.5" Solid Wheels	9.5" Solid Wheels	9.5" Solid Wheels	9.5" Solid Wheels	9.5" Solid Wheels	9.5" Solid Wheels	9.5" Solid Wheels	9.5" Solid Wheels	12.3" Pneumatic Wheels	12.3" Pneumatic Wheels
Warranty	2 Year Residential 1 Year Commercial	2 Year Residential 1 Year Commercial	2 Year Residential 1 Year Commercial	2 Year Residential 1 Year Commercial	2 Year Residential 1 Year Commercial	2 Year Residential 1 Year Commercial	2 Year Residential 1 Year Commercial	2 Year Residential 1 Year Commercial	2 Year Residential 1 Year Commercial	2 Year Residential 1 Year Commercial
Dimensions (L" x W" x H")	33.5 x 26.5 x 27	33.5 x 26.5 x 27	33.5 x 26.5 x 27	33.5 x 26.5 x 27	33.5 x 26.5 x 27	33.5 x 26.5 x 27	33.5 x 26.5 x 27	33.5 x 26.5 x 27	48.5 x 31 x 39.5	48.5 x 31 x 39.5
Unit Weight (lbs)	172	172	177	177	182	187	192	192	363	390

**GENERAC**

Generac Power Systems, Inc.  
S45 W29290 Hwy. 59  
Waukesha, WI 53189  
1-888-GENERAC (1-888-436-3722)