



ULTIMATE CRIMPING ACCURACY

Reduce rework on the job: no more wasted time troubleshooting poor connections or scrapping incorrectly crimped lugs

K05-SYNCR0 K-SERIES CRIMPING TOOL

Eliminates inaccurate crimps caused by mismatched dies; SYNCRO die design for easy one-handed die change



Productivity

- 50% reduced set up time when changing dies
- One-handed operation to rotate dies
- Color-coded, laser-cut, hexagonal rotating dies that prevent inaccurate crimps

Easier

- Small, lightweight and easy to handle
- Synchronized die rotation for effortless die changing
- Easy to get into tight locations

K05-SYNCRO

ULTIMATE CRIMPING ACCURACY



Laser-Cut Dies
More dimensionally accurate than stamped dies

Crimping Capacity
8 - 1/0 AWG

SYNCRO Die Design
The new synchronized die design eliminates crimping errors from mismatched dies

Patent Pending Gear
Minimizes potential for tooth breakage, improving tool durability

SIMPLE TO OPERATE

- Step 1 – Open handles all the way
- Step 2 – Rotate the dial to adjust the dies until you hear a “click”
Find the matching dies by using the color indicator on the dies or the size mark on the dial
- Step 3 – Crimp lugs with cable until the handles are completely closed

Ergonomic Handle Design
New slip guards for easy handling and improve wrist posture

K05-SYNCRO

ORDERING INFORMATION

CAT. NO.	UPC NO.	DESCRIPTION
K05-SYNCRO	06440	Crimping Tool

SPECIFICATIONS

CRIMPING RANGE:	8 to 1/0 AWG
LENGTH:	16"
WEIGHT:	2.6 lbs (1.18 kg)

UL and cUL classified with Anderson®, Blackburn®, Burndy®, ILSCO®, Panduit®, Thomas & Betts® and Penn-Union® copper connectors.

Anderson®, Blackburn®, Burndy®, ILSCO®, Panduit®, Thomas & Betts®, and Penn-Union® are trademarks or registered trademarks of their respective owners.

