



Fuse base, low voltage, 32 A, AC 690 V, BS88/A2, 1P, BS, front connected, black



Powering Business Worldwide™

Part no. 32A RED SPOT FRONT CONNECTED BLACK
Catalog No. RS32H

Delivery program

Product range			Fuse accessory
Basic function			Fuse-holder
Field of application			low voltage
Rated current	I	A	32
Rated voltage			AC 690 V
Construction size			BS88/A2
Description			front connected black
Number of poles			1P
usable for size/applications			fuse-links TIA AAO H07-660
Standard/Approval			BS

Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse base (EC000067)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse systems / Low-Voltage HRC fuse base (ecl@ss10.0.1-27-14-21-06 [AKE278013])			
Construction size			Other
Number of poles			1
Rated current		A	32
Bus-mounting type			No
Swivelling mechanism			No