



SL Series Selection Tables

SECTION 1

Primary Voltage	Secondary Voltage	PART NUMBERS							
		25 VA	50 VA	75 VA	100 VA	150 VA	200 VA	250 VA	350 VA
600	240	SL25AM	SL50AM	SL75AM	SL100AM	SL150AM	SL200AM	SL250AM	SL350AM
600	120/240	SL25AP	SL50AP	SL75AP	SL100AP	SL150AP	SL200AP	SL250AP	SL350AP
600	120	SL25AJ	SL50AJ	SL75AJ	SL100AJ	SL150AJ	SL200AJ	SL250AJ	SL350AJ
600	24	SL25AG	SL50AG	SL75AG	SL100AG	SL150AG	SL200AG	SL250AG	SL350AG
600	12/24	SL25AR	SL50AR	SL75AR	SL100AR	SL500AR	SL200AR	SL250AR	SL350AR
600	12	SL25AE	SL50AE	SL75AE	SL100AE	SL150AE	SL200AE	SL250AE	SL350AE
480	240	SL25CM	SL50CM	SL75CM	SL100CM	SL150CM	SL200CM	SL250CM	SL350CM
480	120	SL25CJ	SL50CJ	SL75CJ	SL100CJ	SL150CJ	SL200CJ	SL250CJ	SL350CJ
480	24	SL25CG	SL50CG	SL75CG	SL100CG	SL150CG	SL200CG	SL250CG	SL350CG
480	12/24	SL25CR	SL50CR	SL75CR	SL100CR	SL150CR	SL200CR	SL250CR	SL350CR
347	120/240	SL25KP	SL50KP	SL75KP	SL100KP	SL150KP	SL200KP	SL250KP	SL350KP
240/480	120	SL25QJ	SL50QJ	SL75QJ	SL100QJ	SL150QJ	SL200QJ	SL250QJ	SL350QJ
240/480	120/240	SL25QP	SL50QP	SL75QP	SL100QP	SL150QP	SL200QP	SL250QP	SL350QP
240/480	12/24	SL25QR	SL50QR	SL75QR	SL100QR	SL150QR	SL200QR	SL250QR	SL350QR
240	120	SL25MJ	SL50MJ	SL75MJ	SL100MJ	SL150MJ	SL200MJ	SL250MJ	SL350MJ
208	120	SL25LJ	SL50LJ	SL75LJ	SL100LJ	SL150LJ	SL200LJ	SL250LJ	SL350LJ
208	24	SL25LG	SL50LG	SL75LG	SL100LG	SL150LG	SL200LG	SL250LG	SL350LG
120/240	24	SL25PG	SL50PG	SL75PG	SL100PG	SL150PG	SL200PG	SL250PG	SL350PG
120	12/24	SL25JR	SL50JR	SL75JR	SL100JR	SL150JR	SL200JR	SL250JR	SL350JR
120	24	SL25JG	SL50JG	SL75JG	SL100JG	SL150JG	SL200JG	SL250JG	SL350JG
120	12	SL25JE	SL50JE	SL75JE	SL100JE	SL150JE	SL200JE	SL250JE	SL350JE

Primary Voltage	Secondary Voltage	PART NUMBERS						
		500 VA	750 VA	1000 VA	1500 VA	2000 VA	3000 VA	5000 VA
600	240	SL500AM	SL750AM	SL1000AM	SL1500AM	SL2000AM		
600	120/240	SL500AP	SL750AP	SL1000AP	SL1500AP	SL2000AP		
600	120	SL500AJ	SL750AJ	SL1000AJ	SL1500AJ	SL2000AJ	SL3000AJ	SL5000AJ
600	24	SL500AG						
600	12/24	SL500AR						
600	12	SL500AE						
480	240	SL500CM	SL750CM	SL1000CM	SL1500CM	SL2000CM		
480	120	SL500CJ	SL750CJ	SL1000CJ	SL1500CJ	SL2000CJ	SL3000CJ	
480	24	SL500CG						
480	12/24	SL500CR						
347	120/240	SL500KP	SL750KP	SL1000KP	SL1500KP	SL2000KP		
240/480	120	SL500QJ	SL750QJ	SL1000QJ	SL1500QJ	SL2000QJ		
240/480	120/240	SL500QP	SL750QP	SL1000QP	SL1500QP	SL2000QP		
240/480	12/24	SL500QR						
240	120	SL500MJ	SL750MJ	SL1000MJ	SL1500MJ	SL2000MJ		
208	120	SL500LJ	SL750LJ	SL1000LJ	SL1500LJ	SL2000LJ		
208	24	SL500LG						
120/240	24	SL500PG						
120	12/24	SL500JR						
120	24	SL500JG						
120	12	SL500JE						

